

OptiChannel
Fiber Accessory
Plug and Play Cassette

Features

- Compact Universal Design
- Ten Gigabit Ethernet Assurance
- Quick and Easy Plug-n-Play Installation

Ordering Information

Description	Color	Catalog Number	UPC
Fiber Optic, Cassette, LCQ-2MPO, OM4,24-Fiber, Type C, Electric Ivory	Violet	OCLCQ50G4CVI	662620607740

Listings

Telcordia GR-326-CORE
TIA-568-C.3
TIA-604-FOCIS

Specifications

Material	Ceramic
Fiber Size	250 Micron
Fiber Type	OM4
Style	LC Quad 24F
Polarity	Type C
Repeatability	0.1 dB
Service Life	500 matings
Temperature Rating	0 °C to 70 °C

Performance

Optical

Total Insertion Loss	Less than 1.1dB (test data included)
----------------------	--------------------------------------

HUBBELL

