

OptiChannel Fiber Accessory Plug and Play Cassette

HUBBELL

Features

- Compact Universal Design
- Ten Gigabit Ethernet Assurance
- Quick and Easy Plug-n-Play Installation

Ordering Information

Description	Color	Catalog Number	UPC
Fiber Optic Cassette, LC-MT, Single Mode, 24-Fiber Strands	Blue	OCLCQSM	662620214450



Listings

Telcordia GR-326-CORE
TIA-568-C.3
TIA-604-FOCIS

Specifications

Material	Ceramic
Fiber Size	250 Micron
Fiber Type	OS2
Style	LC Quad 24F
Polarity	Type A
Repeatability	0.1 dB
Service Life	500 matings
Temperature Rating	0 °C to 70 °C

Performance

Optical	
Total Insertion Loss	Less than 1.5dB (test data included)
Return Loss	More than 50dB

