

Shielded Patch Cord

Features

- 10GbE Application Assurance
- Maximum Bandwidth Beyond 625MHz
- Component Compliant ANEXT Performance
- Qualified to 150% of 802.3bt PoE Current Level

Ordering Information

| Description                   | Color | Catalog Number | UPC          |
|-------------------------------|-------|----------------|--------------|
| 20 ft. Category 6A Patch Cord | Black | PC6ABK20       | 662620204185 |

Listings

ANSI/TIA/EIA-568-C.2 Category 6A component  
ISO 11801/60603-7-41 Category 6A component  
Mechanical: Verified to TIA-568-C.2  
UL Listed 1863

Specifications

|                 |                                                      |
|-----------------|------------------------------------------------------|
| Conductor       | 26AWG FTP                                            |
| Jacket          | Flame-Retardant PVC-CM Rated                         |
| Plug Body       | Polycarbonate UL 94V-0                               |
| Plug Boot       | PVC                                                  |
| Contact Plating | 50 micro-inch Gold with 100 micro-inch under plating |

Performance

Mechanical

|                                |          |
|--------------------------------|----------|
| Cable to plug tensile strength | 20+ lbs. |
| Mating Cycles                  | 2000+    |

Applications

IEEE 802.3an 10GBASE-T  
IEEE 802.3bt 4PPoE Power over Ethernet  
IEEE 802.11ac and IEEE 802.11ax WAP Deployments  
Backward compatible with Cat 5E and 6 hardware and applications

Accessories

|                                 |          |
|---------------------------------|----------|
| Category 6A Component Jack      | SJ6ABK   |
| Unloaded 24-Port Shielded Panel | PSJ24BK2 |
| Unloaded 48-Port Shielded Panel | PSJ48BK2 |

Online Resources

Customer Use Drawing  
eCatalog

