

NEXTSPEED

Category 5e Shielded Patch Cords

HUBBELL

Shielded Patch Cord

Features

- Third Party Verified Category 5E Component
- Plug Optimized for High Density Switch Ports
- Qualified to 150% of 802.3bt PoE Current Level
- 100% Performance Tested

Ordering Information

Description	Color	Catalog Number	UPC
25 ft. Category 5e Shielded Patch Cord	Gray	PS5E25GY	662620288741

Listings

ANSI/TIA/EIA-568-C.2 Category 5e component
ISO 11801/60603-7-41 Category 5e component
Mechanical: Verified to TIA-568-C.2
UL Listed 1863

Specifications

Conductor	26AWG FTP
Jacket	Flame-Retardant PVC-CM Rated
Plug Body	Polycarbonate UL 94V-0
Plug Boot	PVC
Contact Plating	50 micro-inch Gold with 100 micro-inch under plating

Performance

Mechanical

Cable to plug tensile strength	20+ lbs.
Mating Cycles	2000+

Applications

IEEE 802.3ab 1000GBASE-T
IEEE 802.3bt 4PPoE Power over Ethernet
TIA TSB-155 10GbE Over 55 Meters
Backward compatible with Cat 5E hardware and applications



Online Resources

[eCatalog](#)