

inSIGHT™ Data Com Rack Power Distribution Unit  
Basic Power Distribution  
Complete line of single and three phase PDUs

# HUBBELL

## Features

- Locking standard cords to prevent inadvertent disconnection
- High reliability with robotically soldered connections
- Available in Black, Blue, Red, and White



## Ordering Information

| Type                     | Nominal           | Catalog Number | UPC          |
|--------------------------|-------------------|----------------|--------------|
| Basic always on powering | 208V Single Phase | PV72BB20CC-10  | 662620365022 |

## Listings

UL 2416  
EIA 310-E Universal Mounting Pattern  
UL 60950-1

## Specifications

|                        |                                    |
|------------------------|------------------------------------|
| Input Current (A)      | 20 Amp                             |
| Input Power Cord       | L6-20P Plug                        |
| Receptacle group       | 32 C13 & 4 C19 Receptacle          |
| PDU Size               | 72" vertical mount                 |
| Regulatory Approval    | TUV Certified to UL / CSA 609050-1 |
| Operating Environment  | 0 to 60                            |
| Storage Environment    | -25 to 65                          |
| PDU Dimension (inches) | 72 length X 2.2 width X 4.8 depth  |

## Performance

### Low profile

2.18" X 2". Improves airflow

### Receptacle Locking

Prevents inadvertent disconnections. Secured with standard cords

## Online Resources

[eCatalog](#)