

inSIGHT™ Data Com Rack Power Distribution Unit  
Basic Power Distribution  
Complete line of single and three phase PDUs

# HUBBELL

## Features

- Locking standard cords to prevent inadvertent disconnection
- High reliability with robotically soldered connections
- Available in Black, Blue, Red, and White



## Ordering Information

Type	Nominal	Catalog Number	UPC
Basic always on powering	208V Three Phase	PV72BD50GE-10	662620365985

## Listings

UL 2416  
EIA 310-E Universal Mounting Pattern  
UL 60950-1

## Specifications

Input Current (A)	50 Amp
Input Power Cord	CS8365C Plug
Receptacle group	24 C13 & 12 C19 Receptacle
PDU Size	72" vertical mount
Regulatory Approval	TUV Certified to UL / CSA 609050-1
Operating Environment	0 to 60
Storage Environment	-25 to 65
PDU Dimension (inches)	72 length X 2.2 width X 4.8 depth

## Performance

### Low profile

2.18" X 2". Improves airflow

### Receptacle Locking

Prevents inadvertent disconnections. Secured with standard cords

## Online Resources

[eCatalog](#)