

OptiChannel
Simplex Fiber Patch Cords, Riser
FC/APC to FC/APC, Singlemode, OS2



Features

- Precision Zirconia Ferrule, APC Polish
- 100% Tested, Heat Cured Epoxy Termination
- Available in Lengths 1 to 5, 10 meters
- Custom Lengths Quoted to Order

Ordering Information

Description	Cable Type	Catalog Number	UPC
Fiber Patch Cord, Riser, Simplex, FC/APC to FC/APC, OS2, 2M	Simplex Jacket, Yellow	SFRCFCAFCAS2SM	662620614397

Standards

TIA-568.3
TIA-604-FOCIS
Telcordia GR-326-CORE
TIA-492CAAB (OS2, Bend Tolerant)
ANSI/ICEA S-83-596
TIA-598

Specifications

Overall Length	2 meters (6.56 ft)
Ferrule Material	Zirconia Ceramic
Cable Diameter	3.0 mm
Mated Pair Insertion Loss	< 0.35 dB (0.15 dB Typical)
Mated Pair Return Loss	> 65 dB
Polarity	A

Performance

Mechanical

Mating Durability	500 Cycles, < 0.75dB
Minimum Bend Radius	30 mm (1.2 in.)
Operating Temperature Range	0C to 70C (32F to 158F)
Tensile Rating, Short Term	11.24 Lb (50 N)

Applications

10 Gbps/25 Gbps Fiber Channel
Backbone/Horizontal Distribution Interconnect
Data Center Equipment Interconnect

Accessories

Fiber Microscope, 200X	OFSCOPE2
Fiber Cleaning Kit	OFCLEANKT1
Fiber Wipes Dispenser, 90 Sheets	OFWIPES90
Fiber Cleaning Fluid, 3 Oz.	OFCLEANER3OZ

Online Resources

eCatalog

