iStation Phone Plates

Stainless Steel Wall Mount Phone Plates

Features

- Studs Accommodate Any Standard Wall Phone
- Comes With Keystone Jack
- Manufactured From Type 430 Stainless Steel, Brush Finish

Ordering Information

DescriptionColoriStation Stainless Steel WallGrayMount Phone Plate, SingleGang, Recessed Jack

UPC 662620553870

Catalog No.

SP6R

Listings

UL and cUL Listed 1863 ANSI/TIA/EIA-568-C.2 Category 6 component ISO 11801/60603-7-41 Category 6 component Mechanical: Verified to TIA-568-C.2 Mechanical TIA-568-C.2 RoHS Compliant

Specifications

Nose Contact	Beryllium copper with precious metal plating over nickel under plating
IDC Contact	Phosphor bronze with 100 micro-inch tin lead 60/40 plating over nickel under plating
Jack Housing Stuffer Cap	High-impact thermoplastic (UL 94V-0) Lexan® (UL 94 V-0)

Performance

Electrical

Center balanced to Category 6 plug specifications Positive PSACR beyond 300 MHz (channel) 4+Gbs capacity within the bandwidth of 1-250MHz (channel) Qualified to 150% of 802.3bt PoE Current Level

General Information


Backward compatible to lower installed Categories 100% factory tested

Mechanical

Nose Contact Mating Cycles: 2000 IDC Contact Termination: 10x Keystone Latching Force: 25 lbs.

Applications

IEEE 802.3ab 1000GBASE-T IEEE 802.3bt 4PPoE Power over Ethernet TIA TSB-155 10GbE Over 55 Meters



Accessories

1-Punch Tool	TX4P
Category 6 Patch Cord	HC6GN03
Dust Cover	HXJDC25
Ascent Termination Puck	HXTP25
Category 6 Cable	C6SPB

Online Resources

eCatalog



Hubbell Premise Wiring

HUBBELL