



6110PCL5

By Hubbell Premise Wiring
Catalog Number [6110PCL5](#)



Patch Cord, 6-110 Factory Terminated Patch Cords, Cat6 (6-110 to 6-110), 5' Length.

Features

- Plug Housing Includes Built-In Polarization to Ensure Proper Mating Connection to Connecting Blocks
- Angled Conductor Towers Separate Paired Conductors and makes Pair Splitting and Conductor Lacing Simple
- Cable Ties Secure Cable to Cover for Easy Termination and Strain Relief

General

Attenuation	.1dB
Boot Type	Polycarbonate
EU RoHS Indicator	Yes
Item Type	NEXTSPEED 6-110 Connecting Block System
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	Electrical - Terminates 24 to 26 AWG solid or 7-strand twisted-pair cable -
Plug Type	110 Punch Down
Series	Cat 6
Temperature Rating	Per TIA
UPC	662620835884

Dimensions

Outside Diameter 0.218

Electrical Ratings

Voltage Rating 600V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#26-22 AWG

Certifications and Compliance

Industry Standard(s) Exceeds TIA/EIA-568-C.2-1 Category 6 ConNECting Hardware SpecificAtions

Logistics

Carton Quantity 20



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-6110PCL5-SPEC-EN | REV 5/2023