

Cable, SPEEDGAIN« Category 5e,
Riser/REELEX, White

By Hubbell Premise Wiring
Catalog # [C5ERRW](#)



Cable, SPEEDGAIN, Category 5e, Riser/REELEX, White

Application

Riser

General

Cable Rating	Plenum
Catalog Number	C5ERRW
Color	White
Construction	Copper/Insulation Eccentricity Shall Be 90% Minimum
Data Transfer Rate	1GbE
EU RoHS Indicator	Yes
Item Type	SPEEDGAIN Category 5e UTP Cable
Material - Jacket	PVC
Temperature Rating	-20oC to +50oC (-4oF to +122oF)
Type	UTP
UPC	662620201085

Electrical Ratings

Impedance	100
-----------	-----

Conductor Related

Conductor Size	#24 AWG
Conductor Type	Solid Bare Copper
Nema Color	White
Pairs Or Conductor	4-Pair

Logistics

Carton Quantity	1000
-----------------	------

Product Assets

- [Catalog Page - PREM E8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Specifications - C5ERRW Specification Sheet English](#)
- [Specifications - C5ERRW Specification Sheet French](#)