



Copper Solutions, Cable, NEXTSPEED, 10GBE, Riser Rated, Spool, Gray

By Hubbell Premise Wiring
Catalog Number [C6ASRGY](#)



Copper Solutions, Cable, NEXTSPEED, 10GBE, Riser Rated, Spool, Gray.

Application

Riser

General

Cable Rating	Riser
Construction	Copper/Insulation Eccentricity Shall Be 90% Minimum
Data Transfer Rate	10GbE
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6A UTP Cable
Material - Jacket	PVC
Temperature Rating	-20oC to +50oC (-4oF to +122oF)
Type	UTP
UPC	662620202006

Electrical Ratings

Capacitance	5.6 nF/100 Meters @ 1 kHz
Impedance	100

Conductor Related

Conductor Size	#23 AWG
Conductor Type	Solid Bare Copper
Nema Color	Gray
Pairs Or Conductor	4-Pair

Logistics

Carton Quantity	1000
-----------------	------

Product Assets

[Catalog Page - Premise Catalog Page E-4](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-C6ASRGY-SPEC-EN | REV 5/2023