

Patch Cord, Fiber Optic, LC to LC,
Duplex Multi Mode, 50/125, 10GbE, 1
Meter Length



By Hubbell Premise Wiring
Catalog # [DFPCLCLCE1MM](#)

Patch Cord, Fiber Optic, LC to LC, Duplex Multi Mode, 50/125,
10GbE, 1 Meter Length

Application

LC to LC

General

Catalog Number	DFPCLCLCE1MM
Connector Type	LC to LC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	OptiChannel Fiber Patch Cords
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620200408

Dimensions

Display Size	50 Micron, OM3
Length (Meters)	1 m

Pitch	6
-------	---

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Fiber Type	Plenum
Mode	OM3, MM
Wire Type	Multimode

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Specifications - DFPCLCLCE1MM](#)
- [Specifications - DFPCLCLCE1MM Specification Sheet English](#)