

HUBBELL

Premise Wiring

Patch Cord, Fiber Optic, LC to LC, Duplex Multi Mode, 50/125, 10GbE, 3 Meter Length



By Hubbell Premise Wiring
Catalog # [DFPCLCLCE3MM](#)

Patch Cord, Fiber Optic, LC to LC, Duplex Multi Mode, 50/125, 10GbE, 3 Meter Length

Application

LC to LC

General

Catalog Number	DFPCLCLCE3MM
Color	Aqua
Connector Type	LC to LC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	OptiChannel Fiber Patch Cords
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620200422

Dimensions

Display Size	50 Micron, OM3
Length (Meters)	3 m

Pitch 6

Electrical Ratings

Connectivity Plug-In

Conductor Related

Fiber Type Plenum
Mode OM3, MM
Wire Type Multimode

Logistics

Carton Quantity 25

Product Assets

[Specifications - DFPCLCLCE3MM](#)

[Specifications - DFPCLCLCE3MM Specification Sheet English](#)