

Patch Cord, Fiber Optic, ST-Style to SC, Duplex Multi Mode, 50/125, 2 Meter Length



By Hubbell Premise Wiring
Catalog # [DFPCSTSCD2MM](#)

Patch Cord, Fiber Optic, ST-Style to SC, Duplex Multi Mode,
50/125, 2 Meter Length.

Application

ST to SC

General

Catalog Number	DFPCSTSCD2MM
Connector Type	ST to SC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	OptiChannel Fiber Patch Cords
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620821931

Dimensions

Display Size	50 Micron, OM2
Length (Meters)	2 m

Pitch	6
-------	---

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Fiber Type	Plenum
Mode	OM2, MM
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Specifications - DFPCSTSCD2MM](#)
- [Specifications - DFPCSTSCD2MM Specification Sheet](#)