



# Fusion Splice Connector, LC, OM1, Beige, 6 Pack

By Hubbell Premise Wiring  
Catalog Number [FCLCF900M626PK](#)



Fiber Optic, Connector, Fusion Splice, LC, OM1, Pre-Polished, 900, Pack of 6.

## Features

- Pack of 6 connectors
- Each in a protective capsule with cleave protector, extended dust cap, 900 $\mu$ m boot and splice sleeve
- Compatible with fusion splicers having a removable fiber holder
- Metal holder fixture required (sold separately)
- See application table below
- Hubbell fusion splice heat shrink oven, Catalog Number FCSPLHSOVEN is also required for termination

## Application

Interconnect

## General

Color	Beige
Connector Type	LC
Performance	<ul style="list-style-type: none"><li>• Optical - Insertion loss - 0.5dB (0.35dB typical), 0.75dB max</li><li>• Optical - Mating durability - 500 cycles &lt;</li><li>• 0.1dB change</li><li>• Optical - Multimode return loss - 35dB Typ, 22dB minimum</li><li>• Optical - Singlemode return loss - 55dB Typ, 40dB minimum</li><li>• Environmental - Operating temperature - 0 °C to +70 °C</li></ul>
Style	Fusion Splice-On
Sub Brand	OptiChannel
UPC	662620315294

## Electrical Ratings

Connectivity Fiber Optic Connector

## Conductor Related

Fiber Type OM1, MM

## Certifications and Compliance

Industry Standard(s) 

- Telcordia GR-326-CORE
- TIA-568-C.3
- TIA-604-FOCIS

## Logistics

Carton Quantity 20

## Product Assets

[Brochures - Fiber Connectivity Product Guide](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM\_CA-FCLCF900M626PK-SPEC-EN | REV 5/2023