



FCRHD Series Fiber Optic Rack Mount Enclosure, 1U, 12 HD LC Casstette, Unloaded, Grey

By Hubbell Premise Wiring
Catalog Number [FCRHDIUGY](#)



Fiber Products, Rack Mount Panel, 1U, 12 HD Casstette, 12-HD-LC, Unloaded, Grey.

Application

- Ultra High Density for Data Center Applications
- Complete Interconnect system for 10G, 25G, 40G, 50G, 100G, 200G , 400G and Beyond
- Full Compliment of LC-MPO and MPO Cassettes

General

Color	Grey
Compatibility	<ul style="list-style-type: none">• OCLCHD Cassettes• OCHDMTP Adapters
Construction Material - Main	16 gauge cold rolled steel
EU RoHS Indicator	Yes
Enclosure Type	High Density Enclosures
Item Type	Rackmount Enclosure
Material - Mounting Hardware	Rackmount Enclosure
Number Of Ports	144
Style	Unloaded, HD Cassette
UPC	662620238142

Dimensions

Cubic Capacity	565.25 cu.in
Depth	17 in
Height	1.75 in
Width	19 in

Conductor Related

Cable Entry Rear/Sides

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Sell Sheets - FIBERHUBB Ultra Compact Fiber LC to MPO Cassette Modules](#)
[Sell Sheets - FIBERHUBB High Density 144 Port 1U Fiber Enclosure](#)

Related Products

[OCLCHD50G3 - Fiber High Density Cassette, , LC Duplex to MTP, Aqua](#)
[OCLCHD50G4 - Fiber High Density Cassette, , LC Duplex to MTP, Aqua](#)
[OCLCHDSM - Fiber High Density Cassette, , LC Duplex to MTP, Blue](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-FCRHDIUGY-SPEC-EN | REV 5/2023