

PROClick Connector, SC, OS2, Blue,
12 Pack

By Hubbell Premise Wiring
Catalog # [FCSC900KSM12](#)



Features

-
-

Performance

- Optical - Insertion loss - 0.5dB (0.35dB typical), 0.75dB max
- Optical - Mating durability - 500 cycles <
- 0.1dB change
- Optical - Multimode return loss - 35dB Typ, 22dB minimum
- Optical - Singlemode return loss - 55dB Typ, 40dB minimum
- Environmental - Operating temperature - 0 °C to +70 °C

General

Adapter Type	SC
Catalog Number	FCSC900KSM12
Color	Blue
Connector Type	SC
EU RoHS Indicator	Yes
Enclosure Type	Various
Item Type	SC
Material	Ceramic
Material - Mounting Hardware	Fiber Termination, No Polish
Repeatability	0.1 dB
Service Life	500 matings
Specifications	• Cable Type - 900/250 QM • Ferrule Material - Zirconia ceramic, UPC polish • Fiber Type - UPC SM, OS2
Style	PROclick
Sub Brand	OptiChannel
Temperature Rating	0C to 70C
UPC	662620224107

Dimensions

Display Size2.5 mm

Electrical Ratings

Connectivity	Fiber Optic Connector
Insertion Loss	0.75 dB Max
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	OS2, SM

Certifications And Compliance

Industry Standard(s)	• Telcordia GR-326-CORE • TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	1610

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Catalog Page - PREM G3 CatalogPage](#)
[Catalog Page - PREM A7 CatalogPage](#)
[Catalog Page - PREM G03 Catalog Page](#)
[Catalog Page - PREM A07 Catalog Page](#)
[Catalog Page - PREM A8 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - FIBERHUBB PROclick® Fiber Connectors](#)
[Literature - PROclick® Fiber Connectors](#)
[Specifications - FCSC900KSM12 Specification Sheet French](#)
[Specifications - FCSC900KSM12 Specification Sheet English](#)