

HUBBELL Premise Wiring

ST 2Click, ST, OM3, Biege, 12 Pack

By Hubbell Premise Wiring
Catalog # [FCSTF900M50G6PK](#)

Fiber Optic, Connector, Fusion Splice, ST, OM3, Pre-Polished, 900, Pack of 6.



Features

- Pack of 6 connectors
- Each in a protective capsule with cleave protector, extended dust cap, 900Qm boot and splice sleeve
- Compatible with fusion splicers having a removable fiber holder
- Metal holder fixture required (sold separately)
- See application table below
- Hubbell fusion splice heat shrink oven, Catalog Number FCSPLHSOVEN is also required for termination

Application

Interconnect

Performance

- Optical - Insertion loss - 0.5dB (0.35dB typical), 0.75dB max
- Optical - Mating durability - 500 cycles < 0.1dB change
- Optical - Multimode return loss - 35dB Typ, 22dB minimum
- Optical - Singlemode return loss - 55dB Typ, 40dB minimum
- Environmental - Operating temperature - 0 °C to +70 °C

General

Adapter Type	ST
Catalog Number	FCSTF900M50G6PK

Color	Beige
Connector Type	ST
Style	Fusion Splice-On
Sub Brand	OptiChannel
UPC	662620315409

Electrical Ratings

Connectivity Fiber Optic Connector

Conductor Related

Fiber Type OM3, MM

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Telcordia GR-326-CORE • TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity 20

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Specifications - FCSTF900M50G6PK Specification Sheet French](#)
[Specifications - FCSTF900M50G6PK Specification Sheet English](#)



A Hubbell brand