

Fiber, Pigtail, Bundle, FC-Multi
Mode, 12-Fiber Strands, OM2 Fiber,
3 Meter Length



By Hubbell Premise Wiring
Catalog # [FPBKR12FC2M](#)

Fiber, Pigtail, Bundle, FC-Multi Mode, 12-Fiber Strands, OM2
Fiber, 3 Meter Length

Application

FC-MM

General

Catalog Number	FPBKR12FC2M
Connector Type	FC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Fiber Bundle Pig Tail
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620306520

Dimensions

Display Size	OM2
Length (Meters)	3 m
Pitch	12

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Fiber Type	Riser
Mode	OM2
Number of Fibers	12
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Specifications - FPBKR12FC2M Specification Sheet French](#)
[Specifications - FPBKR12FC2M Specification Sheet English](#)