

Fiber, Pigtail, Bundle, SC-Multi
Mode, 12-Fiber Strands, OM3 Fiber,
3 Meter Length

By Hubbell Premise Wiring
Catalog # [FPBKR12SC3M](#)



Fiber, Pigtail, Bundle, SC-Multi Mode, 12-Fiber Strands, OM3
Fiber, 3 Meter Length

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FPBKR12SC3M
Connector Type	SC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	SC-MM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	SC-MM, 12F, OM3
Temperature Rating	TIA 568-C.3
UPC	662620306414

Dimensions

Display Size	50 Micron
Length (Meters)	3 m

Outside Diameter	0.2
Pitch	12

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Fiber Type	Riser
Mode	OM3
Number of Fibers	12
Wire Size	50 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Specifications - FPBKR12SC3M Specification Sheet French](#)
[Specifications - FPBKR12SC3M Specification Sheet English](#)