



Fiber, Pigtail, Bundle, SC-Multi Mode, 12-Fiber Strands, OM4 Fiber, 3 Meter Length

By Hubbell Premise Wiring
Catalog Number [FPBKR12SC4M](#)



Fiber, Pigtail, Bundle, SC-Multi Mode, 12-Fiber Strands, OM4 Fiber, 3 Meter Length.

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Connector Type	SC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	SC-MM Pigtaills
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	SC-MM, 12F, OM4
Temperature Rating	TIA 568-C.3
UPC	662620306421

Dimensions

Display Size	50 Micron
Length (Meters)	3 m
Outside Diameter	0.2
Pitch	12

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Fiber Type	Riser
Mode	OM4
Number Of Fibers	12
Wire Size	50 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-FPBKR12SC4M-SPEC-EN | REV 5/2023