



Fiber, Pigtail, Bundle, LC-Multi Mode, 6-Fiber Strands, OM2 Fiber, 3 Meter

By Hubbell Premise Wiring
Catalog Number [FPBKR6LC2M](#)



Fiber, Pigtail, Bundle, LC-Multi Mode, 6-Fiber Strands, OM2 Fiber, 3 Meter.

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Color	Orange
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	LC-MM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	LC-MM, 6F, OM2
Temperature Rating	TIA 568-C.3
UPC	662620306247

Dimensions

Display Size	50 Micron
Length	118.11 in
Outside Diameter	0.2
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Wire Size	50 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-FPBKR6LC2M-SPEC-EN | REV 5/2023