

Fiber, Pigtail, Bundle, SC-APC,
Single Mode, 6-Fiber Strands, OS2
Fiber, 3 Meter

By Hubbell Premise Wiring
Catalog # [FPBKR6SCA6S](#)



Fiber, Pigtail, Bundle, SC-APC, Single Mode, 6-Fiber Strands, OS2
Fiber, 3 Meter

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FPBKR6SCA6S
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	SC-APC Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	SC-APC, 6F, OS2
Temperature Rating	TIA 568-C.3
UPC	662620306384

Dimensions

Display Size	9 Micron
--------------	----------

Length	118.11 in
Outside Diameter	0.2
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Wire Size	9 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Specifications - FPBKR6SCA6S Specification Sheet French](#)
[Specifications - FPBKR6SCA6S Specification Sheet English](#)