

Fiber Optic, Pigtail, LSZH, LC,  
50Micron, 125 Multi Mode, OM4, 3  
Meter Length

By Hubbell Premise Wiring  
Catalog # [FPLCF3MM](#)

Fiber Optic, Pigtail, LSZH, LC, 50Micron, 125 Multi Mode, OM4, 3  
Meter Length

Application

LC

General

Catalog Number	FPLCF3MM
Connector Type	LC
Construction Material - Main	Glass Fiber
Insulation	PVC
Size	OM4
Sub Brand	Fiber Optic Products
Temperature Rating	0 Degrees C to 75 Degree C
Type	OptiChannel Fiber Pigtails, Single and Bundled
UPC	662620312897

Dimensions



Length (Meters) 3 m

Conductor Related

Mode	OM4, MM
Wire Type	Multimode

Certifications And Compliance

Industry Standard(s)	TIA 568C.4
----------------------	------------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)  
[Specifications - FPLCF3MM Specification Sheet French](#)  
[Specifications - FPLCF3MM Specification Sheet English](#)