

Fiber Optic Pigtail, LC Single Mode,
3) Meter Length

By Hubbell Premise Wiring
Catalog # [FPLCS3SM](#)



Fiber Optic Pigtail, LC Single Mode, Three Meter

Application

LC

General

Catalog Number	FPLCS3SM
Connector Type	LC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620846064

Dimensions

Display Size	SM, OS2
Length (Meters)	3 m

Pitch	6
-------	---

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Mode	OS2, SM
Wire Type	Singlemode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Brochures - Fiber Connectivity Product Guide](#)
- [Specifications - FPLCS3SM Specification Sheet French](#)
- [Specifications - FPLCS3SM Specification Sheet English](#)