



# Fiber Optic Pigtail, SC Multi Mode, 3 Meter Length

By Hubbell Premise Wiring  
Catalog Number [FPSCC3MM](#)



Fiber Optic Pigtail, SC Multi Mode, 3 Meter Length.

## Application

SC

## General

|                    |  |
|--------------------|--|
| Color              | Orange   |
| Connector Type     | SC   |
| EU RoHS Indicator  | Yes  |
| Insulation         | PVC  |
| Item Type          | OptiChannel Fiber Pigtails, Single and Bundled |
| Material           | Glass Fiber                                    |
| Temperature Rating | 0 Degrees C to 75 Degree C                     |
| UPC                | 662620845968                                   |

## Dimensions

|                 |                  |
|-----------------|------------------|
| Display Size    | 62.5 Micron, OM1 |
| Length (Meters) | 3 m              |
| Pitch           | 6                |

## Electrical Ratings

|              |         |
|--------------|---------|
| Connectivity | Plug-In |
|--------------|---------|

## Conductor Related

|           |           |
|-----------|-----------|
| Mode      | OM1, MM   |
| Wire Type | Multimode |

## Logistics

|                 |     |
|-----------------|-----|
| Carton Quantity | 100 |
|-----------------|-----|

## Product Assets

[Brochures - Fiber Connectivity Product Guide](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM\_CA-FPSCC3MM-SPEC-EN | REV 5/2023