

Fiber Optic Pigtail, SC Multi Mode,
10GbE, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FPSCE3MM](#)



Fiber Optic Pigtail, SC Multi Mode, 10GbE, 3 Meter Length

Application

SC

General

Catalog Number	FPSCE3MM
Connector Type	SC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620200347

Dimensions

Display Size	50 Micron, OM3
Length (Meters)	3 m

Pitch	6
-------	---

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Mode	OM3, MM
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Brochures - Fiber Connectivity Product Guide](#)
- [Specifications - FPSCE3MM Specification Sheet English](#)
- [Specifications - FPSCE3MM Specification Sheet French](#)