



Fiber Pigtail, Single Mode, ST, 50/125, 10GHz, 3 Meter Length

By Hubbell Premise Wiring
Catalog Number [FPSTE3MM](#)



Fiber Pigtail, Single Mode, ST, 50/125, 10GHz, 3 Meter Length.

Application

ST

General

Color	Aqua
Connector Type	ST
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620218939

Dimensions

Display Size	50 Micron, OM3
Length (Meters)	3 m
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Mode	OM3, MM
Wire Type	Multimode

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-FPSTE3MM-SPEC-EN | REV 5/2023