



FSP Adapter Panel, FC/PC (Ceramic Split Sleeve), 6-Port, loaded with 6) Single Mode adapters

By Hubbell Premise Wiring
Catalog Number [FSPFC6](#)



FSP Adapter Panel, FC/PC (Ceramic Split Sleeve), 6-Port, loaded with 6) Single Mode adapters.

Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

General

Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) FC Simplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Performance	<ul style="list-style-type: none"> • Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical) • Environmental - Operating temperature - 0 °C to +75 °C
Repeatability	0.1 dB SM
Service Life	500 matings
Temperature Rating	-40C to +85C
UPC	662620806679

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.75 dB Max
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • TIA-568-C.3 • TIA-604-FOCIS
----------------------	--



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-FSPFC6-SPEC-EN | REV 5/2023