

Fiber Optic Panel Adapter, 12-Fiber,
6) LC Duplex, Phosphor Bronze
Sleeves, Black

By Hubbell Premise Wiring
Catalog # [FSPLCDM6BK](#)

Fiber Optic Panel Adapter, 12-Fiber, 6-LC Duplex, Phosphor
Bronze Sleeves

Features

- Premium Quality and High Performance Design

General

Adapter Type	LC Duplex
Catalog Number	FSPLCDM6BK
EU RoHS Indicator	No
Enclosure Type	Various
Item Type	6) LC Duplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Temperature Rating	-40C to +85C
UPC	662620103761

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------



Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

Certifications And Compliance

Industry Standard(s)	• TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Specifications - FSPLCDM6BK Specification Sheet English](#)
[Specifications - FSPLCDM6BK Specification Sheet French](#)