



Fiber Optic Panel Adapter, 72 Fiber, 6) 12-Fiber MTP, Phosphor Bronze Sleeves, Aqua

By Hubbell Premise Wiring
Catalog Number [FSPMTPAQ6](#)

Fiber Optic Panel Adapter, 72 Fiber, 6) 12-Fiber MTP, Phosphor
Bronze Sleeves, Aqua.



Features

- Premium Quality and High Performance Design

Application

Interconnect

General

Color	Aqua
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) MTP
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.2 dB
Service Life	500 matings
Temperature Rating	-40C to +85C
UPC	662620291918

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Insertion Loss 0.30 dB
Return Loss 55

Conductor Related

Fiber Size 125 Micron
Fiber Type Multimode

Certifications and Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-FSPMTPAQ6-SPEC-EN | REV 5/2023