

# HUBBELL Premise Wiring

## Fiber Optic Panel Adapter, 12-Fiber, 3 LC Quad, Zircon Sleeves, Aqua

By Hubbell Premise Wiring  
Catalog # [FSPNLCQS3AQ](#)

Fiber Optic Panel Adapter, 12-Fiber, 3) LC Quad, Zircon Sleeves, Aqua.



### Features

- Premium Quality and High Performance Design

### Application

Interconnect

### Performance

- Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

### General

Adapter Type	LC Quad
Catalog Number	FSPNLCQS3AQ
Environmental Conditions	Indoor
Item Type	LC Quad
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.1 dB SM / 0.2 dB MM
Service Life	500 matings
Single/Multimode	SM/MM
Sub Brand	OptiChannel
Temperature Rating	-40C to +85C

UPC

662620671970

### Electrical Ratings

Insertion Loss	0.30 dB
Return Loss	55

### Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>TIA-568-C.3</li><li>TIA-604-FOCIS</li></ul>
----------------------	---

### Logistics

Carton Quantity	4
-----------------	---

### Product Assets

- [Catalog Page - PREM G10 Catalog Page](#)
- [Catalog Page - PREM G8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - FIBERHUBB N-Series Fiber Panels](#)
- [Specifications - FSPNLCQS3AQ Specification Sheet](#)
- [Specifications - FSPNLCQS3AQ Specification Sheet French](#)