

Fiber Optic Panel Adapter, 12-Fiber,
6 SC Duplex, Zircon Sleeves, Blue

By Hubbell Premise Wiring
Catalog # [FSPNSCDS6B](#)



Performance

- Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Catalog Number	FSPNSCDS6B
Item Type	SC Duplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.1 dB SM / 0.2 dB MM
Service Life	500 matings
Single/Multimode	SM/MM
Sub Brand	OptiChannel
Temperature Rating	-40C to +85C
UPC	662620340340

Electrical Ratings

Insertion Loss	0.30 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)	• TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	4
Pallet Quantity	1800

Product Assets

[Catalog Page - PREM G10 Catalog Page](#)
[Catalog Page - PREM G8 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - FIBERHUBB N-Series Fiber Panels](#)
[Specifications - FSPNSCDS6B Specification Sheet English](#)
[Specifications - FSPNSCDS6B Specification Sheet French](#)