

FSP Adapter Panel, SC Duplex, 3-Port, Unloaded

By Hubbell Premise Wiring
Catalog # [FSPSCD3X](#)

FSP Adapter Panel, SC Duplex, 3-Port, Unloaded

Features

-
-
-

Application

Interconnect

Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	SC Duplex/LC Quad
Catalog Number	FSPSCD3X
Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	3) SC Duplex
Material - Mounting Hardware	Snap-In
Number Of Ports	3
Repeatability	0.1 dB
Service Life	500 matings
Specifications	Dimensions - 1.1" W X 5.1" H



- Finish - Durable black powder coat
 - Material - 16ga cold rolled steel
- Temperature Rating
UPC
- 40C to +85C
662620806730

Dimensions

Display Size
5.1" X 1.1"

Electrical Ratings

Connectivity
Return Loss

Receptacle
55

Conductor Related

Fiber Size
125 Micron

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity
4

Product Assets

[Specifications - FSPSCD3X Specification Sheet English](#)
[Specifications - FSPSCD3X Specification Sheet French](#)