



# Fiber Optic Panel Adapter, 12-Fiber, 6) ST Duplex, Zircon Sleeves, Blue

By Hubbell Premise Wiring  
Catalog Number [FSPSTDS6](#)

Fiber Optic Panel Adapter, 12-Fiber, 6) ST Duplex, Zircon Sleeves, Blue.



## Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

## Application

Interconnect

## General

Color	Blue
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	ST Duplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Performance	<ul style="list-style-type: none"><li>• Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)</li><li>• Environmental - Operating temperature - 0 °C to +75 °C</li></ul>
Repeatability	0.1 dB SM / 0.2 dB MM
Service Life	500 matings
Single/Multimode	SM/MM
Temperature Rating	-40C to +85C
UPC	662620214689

## Dimensions

Display Size 5.1" X 1.1"

## Electrical Ratings

Connectivity Receptacle  
Insertion Loss 0.30 dB  
Return Loss 55

## Conductor Related

Fiber Size 125 Micron  
Fiber Type Singlemode or Multimode

## Certifications and Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

## Logistics

Carton Quantity 4



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM\_CA-FSPSTDS6-SPEC-EN | REV 5/2023