

Fiber Wallmount Cabinet, Hinged,
NEMA 4X, 12 FSP Panel Openings, 6
Splice Tray Capacity

By Hubbell Premise Wiring
Catalog # [FTUOS12SP](#)



Features

- Hinged
- NEMA 4X
- 12 FSP Panel Openings
- 6 Splice Tray Capacity.

Application

OSP Wall Mount

General

Catalog Number	FTUOS12SP
Color	Black
Compatibility	FSP Series Panels and LGX MPO Cassettes
Construction Material - Main	16 gauge cold rolled steel
EU RoHS Indicator	Yes
Enclosure Type	Outdoor 12 Panel Capacity
Item Type	Wall Mounted Enclosures
Material - Mounting Hardware	Pole Mount/Wall Mount
Number Of Ports	288

Style	Unloaded, 12 Panel Capacity
Type	Outside Plant Wall Mount Enclosure
UPC	662620614830

Dimensions

Cubic Capacity	775.18 cu.in
Depth	14 in
Height	4.9 in
Width	11.3 in

Conductor Related

Cable Entry	Rear/Sides
-------------	------------

Product Assets

- [Catalog Page - PREM J9 CatalogPage](#)
- [Catalog Page - PREM J09 Catalog Page](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Specifications - FTUOS12SP Specification Sheet English](#)
- [Specifications - FTUOS12SP Specification Sheet French](#)
- [Specifications - PREMISE_FTUOS12SP_spec](#)