

Patch Cord, Speed Gain, Cat5E,
Slim, Red, 10'

By Hubbell Premise Wiring
Catalog # [HC5ER07](#)



Patch Cord, Speed Gain, Cat 5e, Slim, 10'

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Catalog Number	HC5ER07
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620235882

Dimensions

Length	7 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	• ANSI/TIA/EIA-568-C.2 Category 5E Component • ISO 11801/60603-7-41 Category 5E Component
----------------------	---

Product Assets

[Specifications - HC5ER07 Specification Sheet English](#)
[Specifications - HC5ER07](#)