

# HUBBELL Premise Wiring

## Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 20' Length, Red

By Hubbell Premise Wiring  
Catalog # [HC5ER20](#)



Patch Cords, SPEEDGAIN, Cat 5e, Slim, 20'

### Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

### Specifications

Industry Standard(s)	<ul style="list-style-type: none"><li>• ANSI/TIA/EIA-568-C.2 Category 5E Component</li><li>• ISO 11801/60603-7-41 Category 5E Component</li></ul>
EU RoHS Indicator	Yes

### Conductor

Conductor Type	Copper
Conductor Stranding	Stranded
Wire Size	#24 AWG
Number Of Conductors	8-Conductor

### Current

Voltage Rating	300V AC kV
----------------	------------

### Dimensions

Outside Diameter	0.218
Length	20 ft

### General

Plug Type	RJ45
Type	Standard
Material - Jacket	Flame Redardant PVC
Material - Insulation	Flame Redardant PVC
UPC	662620235912
Color	Red

### Operational

Temperature Rating	Per TIA
--------------------	---------