

Patch Cord, Speed Gain, Cat5E,
Slim, White, 5'

By Hubbell Premise Wiring
Catalog # [HC5EW05](#)



Patch Cord, Speed Gain, Cat5E, Slim, White, 5'

Features

-
-
-
-

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EW05
Color	White
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	• Conductor - 24AWG UTP • Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating • Jacket - Flame-Retardant PVC-CM Rated • Plug Body - Polycarbonate UL 94V-0

Temperature Rating
Type
UPC

- Plug Boot - Polycarbonate UL 94V-0
- Per TIA
Standard
662620236506

Dimensions

Length
Outside Diameter

5 ft
0.218

Electrical Ratings

Voltage Rating

300V AC kV

Conductor Related

Conductor Stranding
Conductor Type
Number of Conductors
Wire Size

Stranded
Copper
8-Conductor
#24 AWG

Certifications And Compliance

- Industry Standard(s)
- ANSI/TIA/EIA-568-C.2 Category 5E Component
 - ISO 11801/60603-7-41 Category 5E Component

Product Assets

[Specifications - HC5EW05 Specification Sheet English](#)
[Specifications - HC5EW05](#)