

HUBBELL Premise Wiring

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 1' Length, Blue

By Hubbell Premise Wiring
Catalog # [HC6AB01](#)

Ascent Patch Cord Cat 6A Slim, 1'



Features

- Third Party Verified Category 6A Component
- Plug Optimized For High Density Switch Ports
- 10-Gigabit Application Assurance
- Qualified to 150% of 802.3bt PoE Current Level

Specifications

EU RoHS Indicator	Yes
Industry Standard(s)	<ul style="list-style-type: none">• ANSI/TIA/EIA-568-C.2 Category 6A Component• ISO 11801/60603-7-41 Category 6A Component

Conductor

Wire Size	#26 AWG
Number Of Conductors	8-Conductor
Conductor Type	Copper
Conductor Stranding	Stranded

Current

Voltage Rating	300V AC kV
----------------	------------

Dimensions

Outside Diameter	0.218
Length	1 ft

General

Plug Type

Color	Blue
Type	Standard
Material - Jacket	Flame Redardant PVC
Material - Insulation	Flame Redardant PVC
Specifications	<ul style="list-style-type: none">• Conductor - 26AWG UTP• Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating• Jacket - Dual Layer Flame-Retardant PVC - CM Rated• Plug Body - Polycarbonate UL 94V-0• Plug Boot - Polycarbonate UL 94V-0

UPC

662620228952

Logistics

Carton Quantity	50
-----------------	----

Operational

Temperature Rating	Per TIA
--------------------	---------

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)