

Copper Solutions, Patch Cords,
Ascent, Cat6A, Slim, 10' Length,
Blue

By Hubbell Premise Wiring
Catalog # [HC6AB10](#)

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 10' Length,
Blue

Features

-
-
-
-

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Catalog Number	HC6AB10
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	• Conductor - 26AWG UTP • Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating • Jacket - Dual Layer Flame-Retardant PVC - CM Rated • Plug Body - Polycarbonate UL 94V-0 • Plug Boot - Polycarbonate UL 94V-0

Temperature Rating	Per TIA
UPC	662620228990

Dimensions

Length	10 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	• ANSI/TIA/EIA-568-C.2 Category 6A Component • ISO 11801/60603-7-41 Category 6A Component
----------------------	---

Product Assets

[Catalog Page - PREM D3 CatalogPage](#)
[Catalog Page - PREM D03 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - HC6AB10 Specification Sheet English](#)
[Specifications - HC6AB10 Specification Sheet French](#)

