



## Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 7' Length, Yellow

By Hubbell Premise Wiring  
Catalog Number [HC6AY07](#)



Copper Solutions, Ascent Patch Cord Cat 6A, Slim, 7'.

### Features

- Third Party Verified Category 6A Component
- Plug Optimized For High Density Switch Ports
- 10-Gigabit Application Assurance
- Qualified to 150% of 802.3bt PoE Current Level

### General

Attenuation	.1dB
Boot Type	PVC
Color	Yellow
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none"><li>• Mechanical - Cable to plug tensile strength - 20+ lbs.</li><li>• Mechanical - Mating Cycles - 2000+</li></ul>
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620231280

### Dimensions

Length	7 ft
Outside Diameter	0.218

### Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

### Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

### Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• ANSI/TIA/EIA-568-C.2 Category 6A Component</li><li>• ISO 11801/60603-7-41 Category 6A Component</li></ul>
----------------------	---

### Product Assets

[Catalog Page - Premise Catalog Page D-3](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM\_CA-HC6AY07-SPEC-EN | REV 5/2023