

## Patch Cord, Speed Gain, Cat6, Slim, Blue, 10'

By Hubbell Premise Wiring

Catalog # [HC6B10](#)

Patch Cord, Speed Gain, Cat6, Slim, Blue, 10'



### Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

### Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

### General

Attenuation	.1dB
Catalog Number	HC6B10
Color	Blue
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620231525

### Dimensions

Length	10 ft
Outside Diameter	0.218

### Electrical Ratings

Voltage Rating 300V AC kV

### Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• ANSI/TIA/EIA-568-C.2 Category 6 Component</li><li>• ISO 11801/60603-7-41 Category 6 Component</li></ul>
----------------------	---

### Logistics

Carton Quantity 25

### Product Assets

<a href="#">Catalog Page - PREM D05 Catalog Page</a>
<a href="#">Catalog Page - PREM D5 CatalogPage</a>
<a href="#">Catalogs - Premise Wiring Catalog</a>
<a href="#">Specifications - HC6B10</a>
<a href="#">Specifications - HC6B10 Specification Sheet English</a>