

Patch Cord, Speed Gain, Cat6, Slim,
Gray, 3'

By Hubbell Premise Wiring
Catalog # [HC6GY03](#)



Patch Cord, Speed Gain, Cat 6,Slim, 3'

Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Catalog Number	HC6GY03
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620232416

Dimensions

Length	3 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	• ANSI/TIA/EIA-568-C.2 Category 6 Component • ISO 11801/60603-7-41 Category 6 Component
----------------------	---

Logistics

Carton Quantity	65
Pallet Quantity	3510

Product Assets

[Catalog Page - PREM D05 Catalog Page](#)
[Catalog Page - PREM D5 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - HC6GY03](#)
[Specifications - HC6GY03 Specification Sheet English](#)