

HUBBELL Premise Wiring

Patch Cord, Speed Gain, Cat6, Slim, Red, 3'

By Hubbell Premise Wiring
Catalog # [HC6R03](#)



Patch Cord, Speed Gain, Cat6, Slim, Red, 3'

Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

Specifications

EU RoHS Indicator	Yes
Industry Standard(s)	<ul style="list-style-type: none">• ANSI/TIA/EIA-568-C.2 Category 6 Component• ISO 11801/60603-7-41 Category 6 Component

Conductor

Wire Size	#24 AWG
Number Of Conductors	8-Conductor
Conductor Type	Copper
Conductor Stranding	Stranded

Current

Voltage Rating	300V AC kV
----------------	------------

Dimensions

Outside Diameter	0.218
Length	3 ft

General

Plug Type	RJ45
Color	Red
Type	Standard
Material - Jacket	Flame Redardant PVC
Material - Insulation	Flame Redardant PVC
UPC	662620233338

Logistics

Carton Quantity	65
-----------------	----

Operational

Temperature Rating	Per TIA
--------------------	---------

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)