

Patch Cord, Speed Gain, Cat6, Slim, White, 3'

By Hubbell Premise Wiring

Catalog # [HC6W03](#)

Patch Cord, Speed Gain, Cat6, Slim, White, 3'

Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Catalog Number	HC6W03
Color	White
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	• Conductor - 24AWG UTP • Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating • Jacket - Flame-Retardant PVC-CM Rated • OD - 0.224 in. • Plug Body - Polycarbonate UL 94V-0 • Plug Boot - Polycarbonate UL 94V-0
Temperature Rating	Per TIA

UPC662620233567

Dimensions

Length	3 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	• ANSI/TIA/EIA-568-C.2 Category 6 Component • ISO 11801/60603-7-41 Category 6 Component
----------------------	---

Logistics

Carton Quantity	65
-----------------	----

Product Assets

- [Catalog Page - PREM D05 Catalog Page](#)
- [Catalog Page - PREM D5 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Specifications - HC6W03](#)
- [Specifications - HC6W03 Specification Sheet English](#)

