



# Fiber Patch Cords, 50-10Ghz, LC-LC Duplex, HD, OM4, 8 Meter Length, Aqua

By Hubbell Premise Wiring  
Catalog Number [HDPCLC50G4M8](#)

Fiber Patch Cords, 50-10Ghz, LC-LC Duplex, HD, OM4, 8 Meter Length, Aqua.



## Application

LC to LC

## General

Color	Aqua
Connector Type	LC to LC
Construction Material - Main	Glass Fiber
Insulation	PVC
Size	50 Micron, OM4
Sub Brand	Fiber Optic Products
Temperature Rating	0 Degrees C to 75 Degree C
Type	OptiChannel Fiber Patch Cords
UPC	662620309132

## Dimensions

Length	26.2 ft
Length (Meters)	8 m

## Conductor Related

Fiber Type	OM4
Wire Type	Multimode

## Certifications and Compliance

Industry Standard(s)	EIA/TIA-455/-604
----------------------	------------------

## Logistics

Carton Quantity	50
-----------------	----



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM\_CA-HDPCLC50G4M8-SPEC-EN | REV 5/2023