



HFCD14 Series Indoor/Outdoor Tight Buffer, 6 strand, I/O Tight Buffer Plenum, OM4, MM , Black Jacket

By Hubbell Premise Wiring
Catalog Number [HFCD14006P4BK](#)



HFCD14 Series Indoor/Outdoor Tight Buffer, 6 strand, I/O Tight Buffer Plenum, OM4, MM , Black Jacket.

Features

- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Cable Rating	I/O Tight Buffer Plenum
Color	Black
Material - Jacket	PVC
Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable
UPC	662620332192

Electrical Ratings

Wavelength 850/1300 Nanometers

Conductor Related

Fiber Size	OM4
Fiber Type	OM4, MM
Number Of Fibers	6

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/ICEA S-83-596• NFPA-262/UL910/CSA FT-6• Telcordia GR-409 and GR-20• TIA-568.3-D
----------------------	---

Product Assets

[Catalog Page](#) - [Premise Catalog Page 1-4](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-HFCD14006P4BK-SPEC-EN | REV 5/2023