

HUBBELL Premise Wiring

HFCD19 Series Indoor/Outdoor Tight Buffer, 24 strand, Plenum, Armored, OS2, SM , Black Jacket

By Hubbell Premise Wiring
Catalog # [HFCD19024PSBK](#)

HFCD19 Series Indoor/Outdoor Tight Buffer, 24 strand, Plenum,
Armored, OS2, SM , Black Jacket.



Features

- Corning ULTRA SMF-28® Singlemode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Multi-Purpose Outdoor Duct To Building Riser Application
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

General

Attenuation	0.5/0.4 Db per Kilometer
Cable Rating	Plenum, Armored
Catalog Number	HFCD19024PSBK
Color	Black
Material - Jacket	PVC
Specifications	<ul style="list-style-type: none">• Armor - Aluminum Interlock• Cable Diameter in (mm) - 0.69 (17.4)• Cable Weight (lb/kft) - 188• Construction - Single Unit, Aramid Strength Member• Fiber Coating - 900 Micron PVC Tight Buffer

Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable
UPC	662620332369

Electrical Ratings

Wavelength	1310/1550 Nanometers
------------	----------------------

Conductor Related

Fiber Size	OS2
Fiber Type	OS2, SM
Number of Fibers	24

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/ICEA S-83-596• NFPA-262/UL910/CSA FT-6• Telcordia GR-409• TIA-568.3-D
----------------------	---

Product Assets

- [Catalog Page - PREM I4 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - Fiber Optic Cable Guide](#)
- [Specifications - HFCD19024PSBK Specification Sheet French](#)