

Category 6 Jack with Cobra-Lock™
Termination

By Hubbell Premise Wiring
Catalog # [HJU6W](#)



NEXTSPEED® Category 6 is a tuned system of structured cabling components designed and balanced to work together to deliver Category 6 performance and headroom beyond 250MHz for 5GBASE-T assurance. NEXTSPEED® Category 6 jacks incorporate Cobra-Lock™ termination which empowers installers to perform fast, repeatable, and reliable terminations.

Features

- Third Party Verified Category 6 Component
- Cobra-Lock™ Termination Reduces Termination Time by Over 75%
- Wires Secured Under Constant Compression
- Easily Re-Terminate
- Qualified to 150% of 802.3bt PoE Current Level

Performance

TIA Cat 6 Component, Third Party Verified

General

Catalog Number	HJU6W
Construction Material - Main Contact	Thermoplastic IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
Contact Point Material	Copper Alloy with Gold Over Plating
EU RoHS Indicator	Yes
Item Type	Modular Jack with Cobra-Lock
Material - Housing	High-impact thermoplastic (UL 94V-0)
Operating Cycles	750+ Plug & 25 Re-Termination Cycles
Series	Cat 6 UTP
Size	0.87 (22) x 0.67 (17) x 1.39 (35)
Specifications	• Wire Compatibility: 24-22 AWG Solid • Plug Compatibility: RJ-11 to 45 • Wire Compatibility: 24-22 AWG Solid
Style	RJ-45 Jack
Temperature Rating	Max Continuous- 75° C, Minimum- -40° C Without

UPC

Impact
662620669687

Dimensions

Dimensions	0.87 (22) x 0.67 (17) x 1.39 (35)
Display Size	Standard Sized Product

Electrical Ratings

Connectivity	RJ45 Jack to Cobra-Lock
Withstand Voltage	1,000 Vac @ 60 Hz

Certifications And Compliance

Industry Standard(s)	• ANSI/TIA/EIA-568 Category 6 component • UL 1863 - Communications-Circuit Accessory • IEC60512-99-002 POE Disconnection Endurance • UL 2043 - Suitable for Air-Handling Spaces • RoHS Compliant
----------------------	--

Logistics

Carton Quantity	24
Number of Pieces in Package	1
Pallet Quantity	7920

Product Assets

[Catalog Page - PREM B03](#) [Catalog Page - PREM B3](#) [CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - HJU6W Specification Sheet English](#)
[Specifications - HJU6W Specification Sheet French](#)